

6000V & 7500 Airwash Carts



6000V Cart

7500 Cart

An Amaircare Airwash system will effectively clean and circulate air throughout your space.

Three-Stage Filtration

Removes particulates, V.O.C.'s and odours using HEPA filters and carbon.

Amaircare Certified

Airwash will produce "maximum indoor air quality" and is suitable for people suffering from chemical sensitivities, asthma or allergies.

Versatile

The AirWash can be used in hotel rooms, when cleaning or vacuuming floors, in print shops or anywhere that elevated V.O.C.'s, particulate or odors are a problem.

Rugged

The AirWash solid metal construction and heavy duty wheels are built for years of trouble free operation in the most demanding of environments.

Easy/Change Filters


Quick access panels allow for easy maintenance.

Safe

The AirWash can safely be used while people are present.. Easy to use, you simply plug it in and turn it on.

Pressurized Rooms

The Airwash Carts can be used to create a negative pressure room. Negative pressure will ensure that possible contamination in the air, stays in that room. This is done by ducting the clean air output outside the room. A duct collar lid is also available for the Airwash Carts for use in creating a positive pressure room. A positive pressure will ensure maximum cleanliness of the room. This is done by ducting the outside air into the unit and leaving the filtered air inside the room.



Durable Metal Cabinet

Greater protection for internal components and filter systems.

No Harmful Production of By Products

Some systems can produce ozone which has found to be harmful to human health.

Highly Efficient

The AirWash is 99.97% efficient on air borne particles over 0.3 microns (1/25,000 of an inch).

Specifications (All Models)

CLASSIFICATION

- Central H.E.P.A. (High Efficiency Particulate Air) 100% Sealed Air Cleaning Device
- U.L. and C.S.A. approved

MATERIALS: 18 gauge satin coat steel

FINISH: Powder coated baked enamel

COLORS: Yellow

MOTOR/FAN

- Thermally protected Class "B" insulated motor
- Designed for continuous operation.
- Run tested for 50,000 hours
- Service: 120 Volt, 60 Hz or 200/230 Volt, 50/60 Hz

CONTROL: On/Off Switch

FILTER LIFE

Stage 1: Foam Filter: 6-12 months

Stage 2: H.E.P.A. Filter: 2-5 years

Stage 3: V.O.C. Filter: 6-12 months

INTAKE:

Alum pre-filter on access door can be removed and steam cleaned.

OUTFLOW:

8" duct fitting(s) on side

6000V Cart

DIMENSIONS: 27" W 26"L 38"H

HEPA SURFACE AREA: 100 sq.ft.

WEIGHT: 92 lbs.

AIR FLOW (C.F.M.): 600

POWER CONSUMPTION: 160 Watts

7500 Cart

DIMENSIONS: 27" W 40"L 38"H

HEPA SURFACE AREA: 200 sq.ft.

WEIGHT: 118 lbs.

AIR FLOW (C.F.M.): 1000

POWER CONSUMPTION: 320 Watts

PREFILTER DOOR

FOAM PRE-FILTER (STAGE 1)

H.E.P.A. FILTER (STAGE 2)

- REMOVES 99.97% OF PARTICULATES FROM 0.3 MICRONS
- 125 SQ. FT SURFACE AREA • LASTS UP TO 5 YEARS

V.O.C. FILTER (STAGE 3)

PROTECTIVE SCREEN FOR H.E.P.A. FILTER

POWERFUL, EFFICIENT MOTOR/FAN


- C.S.A. AND N.T.R.L. (U.L.) APPROVED

METAL CABINET

- DURABLE & EMITS NO TOXINS

METAL CART

- RUGGED CONSTRUCTION FOR MOBILE DURABILITY



Amaircare products available at:

